

ADOX

Silvermax Developer

現像液	現像時間 / 希釈 (20°C)
Adox Silvermax	11 (1+29)
Adox Silvermax @100 (N)	8.5 (1+29)
Adox Silvermax @80 (N-1)	7.25 *1+29)
Adox Silvermax @64 (N-1.5)	6.75 (1+29)
Adox Silvermax @100 (N+1)	11 (1+29)
Adox Silvermax @100 (N+2)	12.25 (1+29)
Adox CHS 100 II @100	8.5 (1+29)
Adox CHS 100 II @125-160	10 (1+29) 高コントラスト
APX 100 NEW (since 2013)	9 (1+24)
APX 400 NEW (since 2013)	11 (1+19)
Ilford FP4+	8 (1+24)
Ilford HP5+ @ 640	10 (1+19)
Kentmere 100	8.5 (1+24)
Kentmere 400	11 (1+19)
Kodak TMax 100	11 (1+24)
Kodak TMax 400 @ 320	11.5 (1+24)
Kodak TriX 400	12 (1+19)
Bergger Pancro 4x5 (回転現像)	11 (1+19)

攪拌: 30/30/1